



HYCD-282

HYCD-282A

Combined Refrigerator and Freezer

Scope of Application

This product is designed to store frozen plasma, biomaterials, vaccines, electronic devices and low temperature tests of special materials, in blood stations, hospitals, epidemic prevention stations, universities, scientific research institutes, electronic chemical industry and other enterprise laboratories.

Innovative Design

- Self-closing Design
- Intelligent Alarm
- Front USB Port
- Safe and Secure

Qingdao Haier Biomedical Co.,Ltd.

In Aotearoa NZ contact:
CCAT Scientific
Tel: 0800 222 812
E-mail: info@ccat.co.nz



Haier Biomedical
International



Haier Biomedical
International



@haiermedicalint



Haier Biomedical
International




Haier Biomedical
International

Product Advantages


-  **Refrigerator & Freezer Combination**
Independent control panel display for refrigerator section and freezer section
-  **Energy Conservation and Environmental Protection**
Frequency conversion compressor and hydrocarbon system, Energy conservation and environmental protection
-  **Multiple Alarms**
High/low temperature, door ajar, power failure, sensor error, low battery, high ambient temperature and remote alarm
-  **High Display Precision**
Refrigerator room display precision is 0.1°C

Product Performance


Refrigerator Cool Down Curve




Refrigerator Warm Up Curve



Freezer Cool Down Curve



Freezer Warm Up Curve



Specifications



Model			HYCD-282	HYCD-282A
Technical Data	Cabinet Type		Upright	Upright
	Climate Class		N	N
	Cooling Type		Refrigorator: Forced air cooling Freezer: Direct cooling	Refrigorator: Forced air cooling Freezer: Direct cooling
	Defrost Mode		Refrigerator: Auto / Freezer: Manual	Refrigerator: Auto / Freezer: Manual
	Refrigerant		Refrigerator: R600a / Freezer: R290	Refrigerator: R600a / Freezer: R290
	Sound Level (dB(A))		43	43
Performance	Temperature Range (°C)		Refrigerator: 2-8 / Freezer: -10~-40	Refrigerator: 2-8 / Freezer: -10~-40
Control	Controller		Microprocessor	Microprocessor
	Display		LED	LED
Electrical Data	Power Supply (V/Hz)		220~240/50/60	220~240/50/60
	Power (W)		410	410
	Electrical Current (A)		2.5	2.5
Dimensions	Capacity (L/Cu.Ft)		Refrigerator: 185/6.5; Freezer: 97/3.4	Refrigerator: 185/6.5; Freezer: 97/3.4
	Net/Gross Weight (approx)	kg	145/160	145/160
	Interior Dimensions (W*D*H)	mm	Refrigerator: 605×510×720 Freezer: 515×465×440	Refrigerator: 605×510×720 Freezer: 515×465×440
	Exterior Dimensions (W*D*H)	mm	735×660×1810	735×660×1810
	Packing Dimensions (W*D*H)	mm	775*720*1930	775*720*1930
	Container Load (20'/40'/40'H)		21/43/43	21/43/43
Alarms	High/Low Temperature		Y	Y
	Door Ajar		Y	Y
	Remote Alarm		Y	Y
	Power Failure		Y	Y
	Sensor Error		Y	Y
	Low Battery		Y	Y
	High Ambient Temp		Y	Y
Accessories	Caster		Y/4	Y/4
	Foot		Y/2	Y/2
	Porthole		Y/2	Y/2
	Shelves/Drawers		Refrigerator: 3/1; Freezer: 0/2	Refrigerator: 3/1; Freezer: 0/2
	Stylus Printer		Optional	Optional
	USB Interface		Y	Y
Others	Certification		CE	CE
Compressor Type			Frequency Conversion Compressor	Frequency Conversion Compressor
Compressor Quantity			2	2